Rittal - The System.

Faster – better – everywhere.



SZ 1581.100 Metal gland plate

State: 25/11/2025 (Source: rittal.com/nz-en)



SZ 1581.100 - Metal gland plate with metric knockouts

Simply knock out the holes for the cable glands using a screwdriver, IP 66 when mounting in the usual position at the bottom.

Features

Model No.	SZ 1581.100
Product description	Simply knock out the holes for the cable glands using a screwdriver.
Material	Sheet steel
Colour	RAL 7035
Note	The allocation of gland plate sizes is indicated on the relevant enclosures
No. of metric knockouts	12 x M20
Dimensions	Width: 221 mm Depth: 90 mm
To fit	Enclosure type: KL
Gland plate	Size: 2
Protection category to IEC 60 529	IP 66 when mounting in the usual position at the bottom
Number knockouts	12
Metric diameter	M20
Packs of	1 pc(s).
Net weight	0.23
Gross weight	0.25
Customs tariff number	73079100
EAN	4028177390843
E-Number Sweden	E3404794
ETIM 9	EC000211
ETIM 8	EC000211

© Rittal 2025

Features

ECLASS 8.0

27142421

© Rittal 2025 3