

Rittal – The System.

Faster – better – everywhere.



EL 2094.200 Captive nuts

State: 23/05/2026 (Source: rittal.com/nz-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



EL 2094.200 - Captive nuts

Captive nut, with M6 thread, with contact

Features

| | |
|--------------------------|--|
| Model No. | EL 2094.200 |
| Design | with contact |
| Product description | For the attachment of rack-mounted electronic equipment, 482.6 mm (19") installed equipment and blanking plates to mounting angles, 482.6 mm (19"). For use with metal thickness from 0.8 – 2.5 mm. Optionally with or without contact of the installed equipment to the 482.6 mm (19") section/enclosure. |
| Dimensions | Thread: M6 |
| For material thicknesses | 0.8 - 2.5 mm |
| Packs of | 50 pc(s). |
| Net weight | 0.2 kg |
| Gross weight | 0.25 kg |
| Customs tariff number | 73181692 |
| ETIM 9 | EC002358 |
| ETIM 8 | EC002358 |
| ECLASS 8.0 | 23110815 |
| Product description | EL Captive nuts, M6, With contact, For metal thickness: 0,8-2,5 mm |