


Rittal – The System.

Faster – better – everywhere.



SG 2372.130

Signal pillar LED compact

State: 4/05/2025 (Source: rittal.com/nz-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SG 2372.130 - Signal pillar LED compact

Extremely long service life of the LEDs, minimal assembly work and low warehousing costs.

Features

| | |
|-----------------------------------|---|
| Model No. | SG 2372.130 |
| Design | 1-stage, red |
| Product description | Transmission angle: 3 x 120°, supplied state: Steady light. Flashing function controllable via PLC |
| Benefits | Complete, ready-to-connect solution Minimal build height Long LED service life Minimal assembly work and warehousing costs |
| Cable entry | Min. cable diameter: 3 mm Max. cable diameter: 6.5 mm |
| Diameter | 72 mm |
| Type of electrical connection | Screw terminals |
| Light | LEDs |
| Rated insulation voltage | < 60 V DC |
| Dimensions | Height: 107 mm |
| Operating temperature range | -20 °C...70 °C |
| Protection category to IEC 60 529 | IP 65 |
| Rated operating voltage | 24 V 24 V (DC) |
| Packs of | 1 pc(s). |
| Net weight | 0.219 |
| Gross weight | 0.233 |
| Customs tariff number | 85311095 |
| EAN | 4028177490130 |

Features

| | |
|------------|----------|
| ECLASS 8.0 | 27371230 |
|------------|----------|

Approvals

| | |
|--------------|---|
| Approvals | UR |
| Explanations | Declaration of conformity Declaration of conformity UK |
