

Rittal – The System.

Faster – better – everywhere.



HD 2410.000 Cable gland HD

State: 23/05/2026 (Source: rittal.com/nz-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



HD 2410.000 - Cable gland HD

HD cable gland IP 68 (5 bar, 30 min.)



Features

Model No.	HD 2410.000
Design	Standard
Benefits	Smooth, solid exterior surfaces effectively prevent the depositing of harmful micro-organisms. Much easier, and therefore cheaper to clean compared with conventional cable glands.
Applications	Manufacturer Clean room technology (e.g. pharmaceuticals) Biotechnology Chemical industry
Material	Nut: Stainless steel 1.4305 (AISI 303) Seal: Conforms to FDA 21 CFR 177.2600
Dimensions	Thread: M12 x 1.5
For cable diameters	3 - 6.5 mm
Operating temperature range	-20 °C...100 °C

Features

IP protection category to IEC 60529	IP 68 (5 bar, 30 min)
Packs of	5 pc(s).
Net weight	0.115 kg
Gross weight	0.123 kg
Customs tariff number	73181900
ECLASS 8.0	27149109
Product description	HD Cable gland, stainless steel 1.4305, size: M12x1,5, for cables Ø 3-6.5 mm, Standard version

Approvals

Explanations	Manufacturer's declaration
--------------	----------------------------