Rittal – The System.

Faster – better – everywhere.





AX 2503.020 Wall mounting bracket

State: 15/12/2025 (Source: rittal.com/nz-en)



AX 2503.020 - Wall mounting bracket for AX sheet steel, KX sheet steel, AX IT, EL

Ideal for convenient one-person assembly of wall-mounted enclosures, even in confined spaces.





Features

Model No.	AX 2503.020
Product description	Ideal for convenient one-person assembly of wall-mounted enclosures, even in confined spaces.
Benefits	Screw-fastened directly from the rear with a self-tapping screw into the enclosure eyelet Simply suspend the wall-mounted bracket from a screw in the wall Different mounting positions allow the wall mounting bracket to be
	tailored to local conditions on site.
	As an alternative to the self-tapping screw, the support may also be secured from the inside using a screw and nut
	Additional option of attaching with a nut for dynamic applications
Material	Sheet steel, zinc-plated
Supply includes	Wall mounting bracket
	Cover cap
	Assembly parts
Wall distance	40 mm
To fit	Enclosure type: AX sheet steel
	KX sheet steel
	AX IT
	EL
	AX wall-mounted enclosure, 3-part

© Rittal 2025

Features

Type rating to UL 50E	Type 1
	Type 3R
	Type 4
	Type 12
Packs of	4 pc(s).
Net weight	0.56
Gross weight	0.568
PCF per pack (cradle-to-gate)	2.2 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	83025000
EAN	4028177938274
E-Number Sweden	E3465270
ETIM 9	EC002625
ETIM 8	EC002625
ECLASS 8.0	27189234

Approvals

Approvals	DNV-GL
	UL + C-UL - FTTA