

Rittal – The System.

Faster – better – everywhere.



SZ 2563.500

Plastic cable gland plates

State: 22/05/2026 (Source: rittal.com/nz-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2563.500 - Plastic cable gland plates with membranes

Simply pierce the plastic and pull through the cable, protection category IP 65 with careful cable entry.

Features

| | |
|--|---|
| Model No. | SZ 2563.500 |
| Product description | Simply pierce the plastic with a sharp object, and pull through the cable. |
| Material | Plastic to UL 94-V0 Halogen free |
| Colour | Similar to RAL 7035 |
| Note | The allocation of gland plate sizes is indicated on the relevant enclosures |
| Dimensions | Width: 534 mm Depth: 149 mm |
| To fit | Enclosure type: AE |
| Gland plate | Size: 5 |
| Protection category to IEC 60 529 | IP 65 |
| No. of cable entries and Ø (mm) min.-max. | 18 x 5-9 16 x 7-12 36 x 10-15 6 x 15-24 2 x 23-30 2 x 26-35 4 x 26-54 1 x 50-110 |
| Packs of | 1 pc(s). |
| Net weight | 0.86 kg |
| Gross weight | 0.96 kg |
| Customs tariff number | 39269097 |
| ETIM 9 | EC000211 |

Features

| | |
|---------------------|---|
| ETIM 8 | EC000211 |
| ECLASS 8.0 | 27142421 |
| Product description | SZ Plastic cable gland plate, with membranes, WD: 534x149 mm, size: 5 |
