


Rittal – The System.

Faster – better – everywhere.



AX 2576.100 Metal gland plate

State: 15/12/2025 (Source: [rittal.com/nz-en](https://www.rittal.com/nz-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AX 2576.100 - Metal gland plate with metric knockouts, for AX

Simply knock out the holes for the cable glands using a screwdriver.

Features

Model No.	AX 2576.100
Product description	Simply knock out the holes for the cable glands using a screwdriver.
Material	Sheet steel
Colour	RAL 7035
Note	The allocation of gland plate sizes is indicated on the relevant enclosures
No. of metric knockouts	2 x M12 10 x M16 8 x M20 18 x M25 4 x M32 4 x M40
Dimensions	Width: 401 mm Depth: 221 mm
To fit	Enclosure type: AX
Gland plate	Size: 6
Protection category to IEC 60 529	IP 66 if installed correctly
Type rating to UL 50E	Type 1 Type 12K
Number knockouts	2 10 8 18 4 4

Features

Metric diameter	M12
	M16
	M20
	M25
	M32
	M40
Packs of	1 pc(s).
Net weight	1.07
Gross weight	1.073
PCF per pack (cradle-to-gate)	5.4 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73079100
EAN	4028177925281
E-Number Sweden	E3465300
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421

Approvals

Approvals	UL + C-UL - FTTA
-----------	------------------