
## Rittal – The System.

Faster – better – everywhere.





## SK 3148.007 Roof-mounted fan, roof vent

State: 18/11/2025 (Source: rittal.com/nz-en)



## SK 3148.007 - Roof-mounted fan, roof vent

May be installed in any sufficiently large roof surface, air throughput 360 m3/h.

## **Features**

| Model No.                               | SK 3148.007  |
|---|--|
| Design                                  | without fan motor  |
| Product modification                    | Mounting cut-outs are not compatible. If reusing the roof plate, adaptor frame 5050.700 is required.                                 |
| Material                                | Sheet steel, spray-finished  |
| Colour                                  | RAL 7035   |
| Supply includes                         | Sealing and assembly parts Drilling template   |
| Dimensions                              | Width: 420 mm<br>Height: 65 mm<br>Depth: 340 mm  |
| Mounting cut-out                        | Cut-out width: 345 mm<br>Cut-out depth: 265 mm   |
| IP protection category to IEC 60<br>529 | IP 43  |
| Note                                    | Via additional installation of the filter holder with filter mat, a protection category of IP 44 is achieved with roof vent 3148.007 |
| Operating temperature range             | -10 °C60 °C  |
| Packs of                                | 1 pc(s).   |
| Net weight                              | 2.644  |
| Gross weight                            | 2.844  |
| Customs tariff number                   | 73269098   |
| EAN                                     | 4028177165335  |
| ECLASS 8.0                              | 27180716   |
|   |  |

© Rittal 2025