

Rittal – The System.

Faster – better – everywhere.



SK 3237.208 Outlet filter

State: 13/05/2026 (Source: rittal.com/nz-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3237.208 - Outlet filter Standard

For ventilation by convection, an outlet filter can be fitted in both the upper and lower sections of the enclosure.



Features

Model No.	SK 3237.208
Product description	For ventilation by convection, an outlet filter can be installed in the upper and lower sections of the enclosure.
Material	ABS
Colour	RAL 9005
Supply includes	Outlet filter Chopped-fibre filter mat
Mounting cut-out	Cut-out width: 92 mm Cut-out height: 92 mm
To fit Model No.	SK 3237.1xx
Dimensions	Width: 116.5 mm Height: 116.5 mm Depth: 16 mm
Protection category NEMA	Type 12 with chopped-fibre filter Type 3 Type 3R with chopped-fibre filter and hose-proof hood
IP protection category to IEC 60529	IP 54 with chopped-fibre filter IP 56 with chopped-fibre filter and hose-proof hood
Packs of	1 pc(s).
Net weight	0.13 kg

Features

Gross weight	0.14 kg
Customs tariff number	39269097
ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706
Product description	SK outlet filter, standard, WHD: 116.5 x 116.5 x 16 mm

Approvals

Approvals	UL + C-UL - FTTA UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK
