

# Rittal – The System.

Faster – better – everywhere.



## SV 3561.000 Plate clamp

State: 28/08/2025 (Source: [rittal.com/nz-en](http://rittal.com/nz-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 3561.000 - Plate clamp

For connecting laminated copper bars, no drilling required.

## Features

Model No.	SV 3561.000
Product description	For connecting laminated copper bars, no drilling required.
Material	Sheet steel
Surface finish	Zinc-plated, passivated
Clamping area for laminated copper bars (W x H)	34 x 10 mm
To fit busbars	60 x 10
To fit busbars	Busbar E-Cu
Packs of	3 pc(s).
Net weight	1.101
Gross weight	1.173
PCF per pack (cradle-to-gate)	4.5 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	85369010
EAN	4028177044371
ETIM 9	EC000001
ETIM 8	EC000001
ECLASS 8.0	27141146

## Approvals

# Approvals

---

Explanations

Declaration of conformity

Declaration of conformity UK

## Tender text

SV plate clamps

for E-CU busbars with 3 - 10 mm thickness.

For bar width: up to 60 mm

Clamping area for laminated copper bars:

34 x 10 mm

Tightening torque

6 - 8 Nm

Material:

Sheet steel, zinc-plated, passivated