

Rittal – The System.

Faster – better – everywhere.



HP 3659.440 TFT display, 15"

State: 8/04/2026 (Source: rittal.com/nz-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



HP 3659.440 - TFT display, 15"

482.6 mm (19") front panel 7 U, TFT LCD 15.1", anti-reflection coated safety glass screen, colours: 16.7 million, maximum resolution 1024 x 768 pixels.

Features

Model No.	HP 3659.440
Product description	Anti-reflection coated safety glass screen
Material	Front panel: Aluminium, powder-coated
Colour	RAL 7035
Dimensions	Width: 482.6 mm Height: 7 U
Interfaces	VGA (D-Sub HD 15-pole)
Note	Depth varies according to the display design (protective glass, touchscreen etc.).
Test specification	Tested to EN 60 950 and EMC directive 89/336/EEC.
Display brightness	250 cd/m ²
Contrast ratio	300 : 1
On Screen Display (OSD)	Membrane keyboard on the front
Reading angle left/right	160 °
Resolution of display	1024 x 768 pixels
Number of colours	16,700,000
Resolution of controller	VGA SVGA
Packs of	1 pc(s).
Net weight	8.36 kg
Gross weight	8.8 kg
Customs tariff number	85286200
ECLASS 8.0	27189234