
# Rittal - The System.

Faster - better - everywhere.





# AS 4050.757 Wire end ferrules

State: 30/10/2025 (Source: rittal.com/nz-en)



## AS 4050.757 - Wire end ferrules loose

With plastic collar.

#### **Features**

Model No.	AS 4050.757
Product description	With plastic collar.
Technical specifications	Heat-resistant to 105 °C
Material	E-Cu, galvanic tin-plated Plastic collar: Polypropylene
Colour	Turquoise
Length	8 mm
AWG	22
Internal diameter	2 mm
Rittal colour code	Yes
For cross-section	0.34 mm²
Note	UL-certified in conjunction with the relevant tools, such as crimping machines. For bespoke advice, please contact your Rittal sales consultant.
Standards	AEH DIN 46228
Delivery form	Loose
Packs of	500 pc(s).
Net weight	0.5
Gross weight	0.026
Customs tariff number	85369010
EAN	4028177815797
ETIM 9	EC000005
ETIM 8	EC000005

© Rittal 2025

### Features

ECLASS 8.0 36659290

## **Approvals**

Approvals UL + C-UL (listed) UR

© Rittal 2025

3