

Rittal – The System.

Faster – better – everywhere.



AS 4054.140 Crimping pliers

State: 28/05/2026 (Source: rittal.com/nz-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4054.140 - Crimping pliers for ring terminals

For use with insulated ring terminals and connectors



Features

| | |
|---------------------|---|
| Model No. | AS 4054.140 |
| Design | Angled |
| Product description | For use with insulated ring terminals and connectors. |
| Benefits | Clear allocation of cross-sections, thanks to colour coding on the dies Releasable ratchet Releases as soon as the required pressure is reached, to prevent underpressing |
| Material | High-quality special tool steel |
| Surface finish | Matt, plated |
| Colour | Handle: Anthracite and Rittal Power Pink |
| Compression | Oval crimp |
| Dimensions | Height: 59 mm Length: 198 mm |
| AWG | 22 - 14 |
| For cross-section | 0.75 - 2.5 mm ² |
| Packs of | 1 pc(s). |
| Net weight | 0.42 kg |
| Gross weight | 0.44 kg |

Features

| | |
|-----------------------|--|
| Customs tariff number | 82032000 |
| ETIM 9 | EC000168 |
| ETIM 8 | EC000168 |
| ECLASS 8.0 | 21043811 |
| Product description | Crimping plier 0.5 - 2,5 mm ² , Oval-c. |
