

Rittal – The System.

Faster – better – everywhere.



AS 4054.141 Crimping pliers

State: 15/05/2026 (Source: rittal.com/nz-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4054.141 - Crimping pliers for ring terminals

For use with insulated ring terminals and connectors

Features

Model No.	AS 4054.141
Design	Straight
Product description	For use with insulated ring terminals and connectors.
Benefits	Clear allocation of cross-sections, thanks to colour coding on the dies Releasable ratchet Releases as soon as the required pressure is reached, to prevent underpressing
Material	High-quality special tool steel
Surface finish	Matt, plated
Colour	Handle: Anthracite and Rittal Power Pink
Compression	Oval crimp
Dimensions	Height: 68 mm Length: 256 mm
AWG	22 - 10
For cross-section	0.75 - 6 mm ²
Packs of	1 pc(s).
Net weight	0.64 kg
Gross weight	0.68 kg
Customs tariff number	82032000
ETIM 9	EC000168
ETIM 8	EC000168
ECLASS 8.0	21043811
Product description	Crimping plier 0.5 - 6 mm ² , Oval-Cr.