

Rittal – The System.

Faster – better – everywhere.



AS 4055.480 Hole punch set, metric

State: 2/07/2026 (Source: rittal.com/nz-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.480 - Hole punch set, metric for sheet steel

For punching round cut-outs

Features

| | |
|--|---|
| Model No. | AS 4055.480 |
| Design | With 3 cutting points |
| Product description | For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch. |
| Supply includes | 5 female dies 5 male dies Plastic case |
| Machinable material | Sheet steel |
| Maximum machinable material thickness, sheet steel | 2 mm 2 mm 2 mm 2 mm 3 mm |
| Ø punch | 16.2 mm 20.4 mm 25.4 mm 32.5 mm 40.5 mm |
| For threads | M16 M20 M25 M32 M40 |
| Note | When operating with wrenches, tension screws with ball bearings should be used. |

Features

| | |
|--|--|
| Suitable for hydraulic bolt order number | 4055.661 4055.661 4055.661 4055.661 4055.663 |
| Packs of | 1 pc(s). |
| Net weight | 0.95 kg |
| Gross weight | 0.98 kg |
| Customs tariff number | 82073010 |
| ETIM 9 | EC002121 |
| ETIM 8 | EC002121 |
| ECLASS 8.0 | 21049047 |
| Product description | Sheet metal punches set, metric Ø 16,2/20,4/25,4/32,5/40,5 |
