

Rittal – The System.

Faster – better – everywhere.



AS 4055.554

Splitter hole punch, round

State: 25/07/2025 (Source: rittal.com/nz-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.554 - Splitter hole punch, round for sheet steel, with triple splitting

For punching round cut-outs

Features

| | |
|--|---|
| Model No. | AS 4055.554 |
| Design | With triple splitting |
| Product description | |
| Supply includes | Female dies Male dies |
| Machinable material | Sheet steel |
| Maximum machinable material thickness, sheet steel | 3 mm |
| Ø punch | 54 mm |
| Note | When operating with wrenches, tension screws with ball bearings should be used. Other sizes, see splitter hole punch, round, stainless steel |
| Suitable for hydraulic bolt order number | 4055.663 |
| Tension screw (Ø x L) | 19 x 75 mm |
| Hydraulic tension screw Ø | 19 mm |
| Packs of | 1 pc(s). |
| Net weight | 0.628 |
| Gross weight | 0.701 |
| Customs tariff number | 82073010 |
| EAN | 4028177808799 |
| ETIM 9 | EC000156 |

Features

| | |
|------------|----------|
| ETIM 8 | EC000156 |
| ECLASS 8.0 | 21049047 |