

Rittal – The System.

Faster – better – everywhere.



VX 5301.330

Gland plate modules, vented

State: 1/06/2026 (Source: rittal.com/nz-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 5301.330 - Gland plate modules, vented for VX IT

For closing the base

Features

| | |
|-------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No. | VX 5301.330 |
| Product description | For closing the base |
| Benefits | Large perforated section to support passive climate control of the enclosure Filter mat slides in from above for easy replacement |
| Material | Sheet steel |
| Surface finish | Zinc-plated |
| Supply includes | Gland plate modules, vented Filter mat Assembly parts |
| Assembly instruction | Several gland module plates must be combined to seal the base completely in the VX IT The gland plate module may be combined in exchange with other base modules with a depth of 237.5 mm. |
| Dimensions | Depth: 237.5 mm |
| To fit | Enclosure type: VX IT Width: = 600 mm |
| Packs of | 1 pc(s). |
| Net weight | 1.44 kg |
| Gross weight | 1.64 kg |
| PCF per pack (cradle-to-gate) | 6.2 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 94039910 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189261 |

Features

Product description

VX IT gland plate module, ventilated, for width 600 mm, W x D 600 x 237.5 mm, sheet steel