


Rittal – The System.

Faster – better – everywhere.



DK 5301.542

Sheet steel door, one-piece, solid

State: 23/05/2026 (Source: rittal.com/nz-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5301.542 - Sheet steel door, one-piece, solid for VX IT

To replace existing doors.



Features

| | |
|-------------------------------------|--|
| Model No. | DK 5301.542 |
| Product description | To replace existing doors. |
| Material | Sheet steel |
| Surface finish | Spray-finished |
| Colour | Door: RAL 7035 Comfort handle VX: RAL 9005 |
| Supply includes | Door with comfort handle for semi-cylinders with security lock 3524 E 4 x 130° hinges, inside Assembly parts |
| Assembly instruction | For a door opening angle of 180° when baying, a 180° baying hinge is required |
| Note | Door opening angle for stand-alone siting: max. 165° Door opening angle when baying: max. 110° |
| IP protection category to IEC 60529 | IP 55 |

Features

| | |
|-------------------------------|---|
| To fit | Enclosure type: VX IT Width: = 800 mm Height: = 2,200 mm |
| Packs of | 1 pc(s). |
| Net weight | 34.45 kg |
| Gross weight | 35.4 kg |
| PCF per pack (cradle-to-gate) | 134.9 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 94039910 |
| ETIM 9 | EC000747 |
| ECLASS 8.0 | 27182204 |
| Product description | Sheet steel door, one-piece, solid for VX IT, to replace existing doors. For enclosure width 800 mm, for enclosure height 2,200 mm, sheet steel, spray-finished |