

Rittal – The System.

Faster – better – everywhere.



VX 5302.161

Depth stays

State: 10/02/2026 (Source: ittal.com/nz-en)



FRIEDHELM LOH GROUP

VX 5302.161 - Depth stays for 482.6 mm (19") mounting angles

L-shaped mounting angles, also for accommodating server system installation kits.

Features

| | |
|----------------------|--|
| Model No. | VX 5302.161 |
| Design | for VX IT 482.6 mm (19") mounting angles, dynamic |
| Product description | To accommodate 19" mounting angles. |
| Benefits | Particularly high load capacity up to 15,000 N Enhanced stability thanks to improved load distribution Symmetrical or asymmetrical installation supported More space for cable routing or integration of a Liquid Cooling Unit (LCU) with one-sided, asymmetrical (laterally offset) installation Ideal for integrating 482.6 mm (19") mounting angles for alternative installation with 21", 23", or 24" components |
| Material | Sheet steel |
| Surface finish | Spray-finished |
| Colour | RAL 9005 |
| Supply includes | Depth stays Assembly parts 4 support strips (2 top, 2 bottom) |
| Assembly instruction | For the attachment of mounting angles in enclosures that are greater than 1000 mm deep and greater than 600 mm wide, an additional support rail for VX IT is required |
| To fit | Enclosure type: VX IT, dynamic Width: > 600 mm Depth: = 1,000 mm |
| Packs of | 4 pc(s). |
| Net weight | 10 |
| Gross weight | 10.36 |

Features

| | |
|-------------------------------|--|
| PCF per pack (cradle-to-gate) | 39.5 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 73269098 |
| EAN | 4028177955585 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189261 |

Approvals

| | |
|--------------|----------------------------|
| Explanations | Manufacturer's declaration |
|--------------|----------------------------|