

Rittal – The System.

Faster – better – everywhere.



DK 5501.400

Slide rail, 2 U, static installation

State: 23/05/2026 (Source: rittal.com/nz-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5501.400 - Slide rail, 2 U, static installation for VX IT

For mounting between 482.6 mm (19") mounting angles.

Features

Model No.	DK 5501.400
Product description	System punchings for mounting accessories and cooling active components.
Applications	For mounting on a 482.6 mm (19") mounting level
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
Length	150 mm
Installation options	for 482.6 mm (19") mounting angles, standard for 482.6 mm (19") mounting angles, dynamic
Load capacity	300 N, static
Packs of	2 pc(s).
Net weight	0.62 kg
Gross weight	0.703 kg
PCF per pack (cradle-to-gate)	2.6 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098
ETIM 9	EC002620
ECLASS 8.0	27189261
Product description	DK Slide rail, 2 U, D: 150 mm, 30 kg, static, For a 482.6 mm (19") attachment level, static installation, for 482.6 mm (19") system punchings