

Rittal – The System.

Faster – better – everywhere.



DK 7109.200

Light, 1 U

State: 15/05/2025 (Source: rittal.com/nz-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7109.200 - Light, 1 U

Ready-to-connect light for installation in the 482.6 mm (19") mounting angles. Fluorescent tube 8 W, 230 V, 50 Hz.

Features

| | |
|-------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No. | DK 7109.200 |
| Product description | Ready-to-connect light for installation in the 482.6 mm (19") mounting angles. The slot attachment additionally allows it to be fastened to the 25 mm system punchings. |
| Material | Aluminium, anodised Plastic |
| Supply includes | Light, 1 U Light Connection cable with earthing-pin plug: Assembly parts |
| Power consumption | 8 W |
| Length of connection cable | 2.5 m |
| Connection options | Integral connection cable with earthing-pin connector |
| Light | Fluorescent tubes |
| Switch (type) | Integral, on/off |
| Rated impulse withstand voltage, phase to earth | 1000 V AC |
| Rated impulse withstand voltage, phase to phase | 500 V AC |
| Rated insulation voltage | 500 V DC/1s |
| Dimensions | Width: 482.6 mm |
| Rated operating voltage | 230 V, 1~, 50 Hz |
| Packs of | 1 pc(s). |
| Net weight | 1.05 |

Features

| | |
|-----------------------|---------------|
| Gross weight | 1.193 |
| Customs tariff number | 94054990 |
| EAN | 4028177305557 |
| ECLASS 8.0 | 27189241 |

Approvals

| | |
|--------------|---------------------------|
| Approvals | TÜV |
| Explanations | Declaration of conformity |

Tender text

Enclosure light for 482.6 mm (19 inch) rack with cable and earthed plug, 8 W

1 light with switch, includes 8 W fluorescent lamp, 2.5 m connection cable with fitted earthing-pin plug.

Material: Aluminium, anodised plastic