

# Rittal – The System.

Faster – better – everywhere.



## DK 7240.300

### Socket strip

State: 5/03/2026 (Source: [rittal.com/nz-en](https://www.rittal.com/nz-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7240.300 - Socket strip with ammeter

For measuring the power consumption of the connected consumers, pin patterns: "earthing pin", various mounting options

## Features

|                            |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
|----------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No.                  | DK 7240.300                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| Product description        | The socket strip with ammeter measures the active power of the connected equipment. The 482.6 mm (19") long socket strip may optionally be mounted on the 482.6 mm (19") mounting frame, on the enclosure frame or in the rear section of wall-mounted distributors. The installation bracket may be mounted in four different positions for variable mounting. Without additional mounting accessories, the socket strip may be inserted into all sections with a 25 mm pitch pattern. |
| Material                   | Aluminium section, natural anodised<br>Socket inserts: Polycarbonate                                                                                                                                                                                                                                                                                                                                                                                                                    |
| Supply includes            | Socket strip<br>Two installation brackets<br>Assembly parts<br>With 3 m connection cable (wire end ferrules)                                                                                                                                                                                                                                                                                                                                                                            |
| Design                     | With ammeter                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
| Sockets                    | 7 x D, earthing-pin (type F, CEE 7/4)                                                                                                                                                                                                                                                                                                                                                                                                                                                   |
| Dimensions                 | Height: 45 mm<br>Depth: 50 mm<br>Length: 482.6 mm                                                                                                                                                                                                                                                                                                                                                                                                                                       |
| Length of connection cable | 3 m                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
| Mounting dimensions        | 464.1 mm                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |
| Rated operating voltage    | 230 V AC, 50 Hz                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
| Rated voltage              | 230 V AC, 50 Hz                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
| Rated current (max.)       | 16 A                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |

# Features

|                       |                                                                                                                                                                    |
|-----------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Installation options  | Components with a 25 mm pitch pattern<br>Enclosure frame<br>IT wall-mounted distributor, at the rear, horizontal (adequate width provided)<br>482.6 mm (19") level |
| Colour of socket      | Grey                                                                                                                                                               |
| Packs of              | 1 pc(s).                                                                                                                                                           |
| Net weight            | 0.859 kg                                                                                                                                                           |
| Gross weight          | 1.18 kg                                                                                                                                                            |
| Customs tariff number | 85366990                                                                                                                                                           |
| ECLASS 8.0            | 27142604                                                                                                                                                           |

# Approvals

|              |                           |
|--------------|---------------------------|
| Explanations | Declaration of conformity |
|--------------|---------------------------|

# Tender text

Socket strip, 7 way multi-appliance receptacle earthed  
max 16A/socket

2 angle brackets are needed to fix the socket strip in  
the network enclosure.

The socket strip has 7 earthed sockets fitted in it.

The ammeter shows the flowing current with a two digit  
7 segment display. It is an aluminium section, natural  
anodised enclosure. The socket cups are made from  
polycarbonate.

Technical specifications:

- Dimensions 482.6 length, 44.45 mm width,  
44.45 mm height
- Rated current: 16 A
- Rated voltage: 230V
- Protection category: IP20
- Conformity: CE following directive 72/73/EWG,  
ROHS following directive 2002/95/EC
- Safety: DIN EN 60950-1
- Connection cables: 3 m, grey, without connector,  
H05VV-F3G1.5