

# Rittal – The System.

Faster – better – everywhere.



## DK 7502.660 QuickBox

State: 6/06/2025 (Source: [rittal.com/nz-en](http://rittal.com/nz-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7502.660 - QuickBox

Wall-mounted enclosure with optimum use of the interior space thanks to side, vertical installation of the 482.6 mm (19") components and removable cover. Status monitoring via side viewing window.

## Features

Model No.	DK 7502.660
Design	with vertical 482.6 mm (19") level
Product description	Wall-mounted enclosure with optimum use of the interior space thanks to side installation of the 482.6 mm (19") components. Status monitoring via side viewing window.
Material	Wall mounting plate with mounting brackets: Sheet steel, 2.0 mm Enclosure cover: Sheet steel, 1.0 mm, with single-pane safety glass at the side, 3 mm
Surface finish	Powder-coated
Colour	RAL 7035
Supply includes	Wall section: with pre-configured 482.6 mm (19") mounting brackets for accommodating equipment at the side. Brush strip for cable entry at the bottom and top. Enclosure cover: Side vent slots to support passive climate control. The enclosure is secured via two security locks positioned at the sides.
Units	6 U
Dimensions	Width: 600 mm Height: 631 mm Depth: 360 mm
Installation depth	348 mm
Depth of wall section	621 mm
Width wall section	595 mm
Basic material	Sheet steel
Note on Model No.	Extended delivery times.

# Features

Packs of	1 pc(s).
Net weight	22.085
Gross weight	23.25
Customs tariff number	94032080
EAN	4028177304048
ECLASS 8.0	27180208

# Tender text

Wall-mounted enclosure with vertical 482.6 mm  
(19 inch) level

## Enclosure:

6 U wall-mounted enclosure, consisting of wall section  
and enclosure cover

Wall section: Wall mounting plate with  
pre-configured 482.6 mm (19 inch) mounting brackets on  
the left and right hand side for side accommodation of  
mounting components.

May be retrofitted to 12 U 482.6 (19 inch) front  
side, horizontal installation position of components.

Four holes for direct wall-mounting or by means of  
optional wall mounting brackets.

Enclosure cover with vent slots for passive  
ventilation, with security locks 12321 on the left and  
right hand side, with side single-pane safety glass,  
3 mm.

Apertures for cable entry at top and bottom, with brush  
inserts.

## Material:

Wall section, enclosure cover of sheet steel,  
single-pane safety glass ESG 3mm

## Surface finish:

Electrophoretic dipcoat primed, spray-finished in  
RAL 7035

## Dimensions (W x H x D):

600 x 631 x 360 mm / (6 U)