

**Rittal – The System.**

Faster – better – everywhere.



**DK 7712.135**

**Wall-mounted enclosures EL, 3-part**

State: 27/06/2026 (Source: [rittal.com/nz-en](http://rittal.com/nz-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7712.135 - Wall-mounted enclosures EL, 3-part with punched rails and mounting angles, depth-variable

Wall-mounted enclosure 3-part, pre-configured with: Solid gland plate, top and bottom, punched rails, C rails, wall mounting bracket. Protection category IP 55.

## Features

|                     |  |
|---------------------|--|
| Model No.           | DK 7712.135  |
| Design              | Wall-mounted enclosures IT<br>with punched rails and mounting angles, depth-variable   |
| Product description | Wall-mounted enclosure with optimum accessibility due to hinged part.  |
| Material            | Wall and hinged part: Sheet steel, 1.5 mm<br>Viewing window: Single-pane safety glass, 3 mm  |
| Surface finish      | Powder-coated  |
| General colour      | RAL 7035   |
| Colour              | Wall and hinged part: RAL 7035<br>Glazed door: RAL 7035/7015 (slate grey)  |
| Supply includes     | Wall section with solid gland plate, top and bottom, two vertical mounting rails and C rail, horizontal, for cable clamping<br>Hinged part with 25 mm pitch pattern of holes in the front and rear frame, and two 482.6 mm (19") mounting angles at the front, infinitely depth-variable<br>4 wall mounting brackets 10 mm<br>Designer glazed door<br>1 double-kit key no. 5<br>Mini-comfort handle for lock inserts<br>Security lock 3524 E |
| Units               | 12 U   |
| Dimensions          | Width: 600 mm<br>Height: 612 mm<br>Depth: 473 mm   |
| Installation depth  | 420 mm   |

# Features

---

|                                       |  |
|---------------------------------------|--|
| Clearances                            | Clearance width: 502 mm<br>Clearance height: 549 mm  |
| Depth hinged part                     | 316 mm   |
| Depth of wall section                 | 135 mm   |
| IK Code                               | IK08   |
| Load capacity of hinged part (static) | 600 N  |
| Basic material                        | Sheet steel  |
| Protection category to IEC 60 529     | IP 55  |
| Packs of                              | 1 pc(s).   |
| Net weight                            | 34.2 kg  |
| Gross weight                          | 36 kg  |
| Customs tariff number                 | 94032080   |
| ETIM 9                                | EC000261   |
| ECLASS 8.0                            | 27142408   |
| Product description                   | DK Wall-mounted enclosures, 3-part, WHD: 600x612x473 mm, 12 U, With punched rails, and mounting angles, depth-variable |

# Approvals

---

|           |                    |
|-----------|--------------------|
| Approvals | UL + C-UL (listed) |
|-----------|--------------------|

# Tender text

Pre-assembled wall-mounted distributor, 12 U

Enclosure:

Three-part wall-mounted distributor enclosure,  
consisting of:

Wall-mounted unit with 2 vertical mounting rails and one horizontally mounted C rail for cable clamping, exchangeable top and bottom gland plates, solid, hinged part with two infinitely adjustable 482.6 mm (19") mounting angles, mounted on C rails, with all-round 25 mm punched profile in front and rear frames, glazed door design with mini comfort handle for lock inserts, with 3524E security lock that can be changed for mini comfort handle for semi-cylinder (option), 4 x 10 mm wall-mounting brackets included.

Protection category: IP 55 to EN 60 529/10.91

Hinged part load capacity: 60 kg

Material:

Enclosure: Sheet steel 1.5 mm

Viewing window: 3 mm single-pane safety glass

Surface finish:

Electrophoretic dipcoat, spray finished,  
enclosure RAL 7035, glazed door RAL 7035/7015

Dimensions (W x H x D):

600 x 612 x 473 mm, 12 U