

Rittal – The System.

Faster – better – everywhere.



DK 7721.535

Wall-mounted enclosures EL, 3-part

State: 25/08/2025 (Source: [rittal.com/nz-en](https://www.rittal.com/nz-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7721.535 - Wall-mounted enclosures EL, 3-part pre-configured with mounting angles, depth-variable

Wall-mounted enclosure 3-part, pre-configured with: Solid gland plate, top, with brush strip at the bottom, mounting rails, C rails, outlet filter, earth rail, wall-mounting bracket

Features

Model No.	DK 7721.535
Design	Wall-mounted enclosures IT pre-configured with mounting angles, depth-variable
Product description	Wall-mounted enclosure with optimum accessibility due to hinged part.
Material	Wall and hinged part: Sheet steel, 1.5 mm Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
General colour	RAL 7035
Colour	Wall and hinged part: RAL 7035 Glazed door: RAL 7035/7015 (slate grey)
Supply includes	Wall section with solid gland plate at the top and brush strip at the bottom, two vertical mounting rails and C rail, horizontal, for cable clamping Hinged part with 25 mm pitch pattern of holes in the front and rear frame, two 482.6 mm (19") mounting angles at the front, infinitely depth-variable, and side outlet filters on the left and right Earth rail with star earthing Designer glazed door 1 double-kit key no. 5 Wall mounting bracket, 10 mm, reinforced Comfort handle for lock inserts and 2-point locking Security lock 3524 E
Units	21 U

Features

Dimensions	Width: 600 mm Height: 1,012 mm Depth: 673 mm
Installation depth	620 mm
Clearances	Clearance width: 502 mm Clearance height: 949 mm
Depth hinged part	516 mm
Depth of wall section	135 mm
IK Code	IK08
Load capacity of hinged part (static)	750 N
Basic material	Sheet steel
Protection category to IEC 60 529	IP 54 in conjunction with solid gland plate top and bottom
Packs of	1 pc(s).
Net weight	57
Gross weight	59
Customs tariff number	94032080
EAN	4028177551039
E-Number Sweden	E7239962
ETIM 9	EC000261
ECLASS 8.0	27142408

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------