


Rittal – The System.

Faster – better – everywhere.



DK 7824.225 Sheet steel door

State: 12/03/2026 (Source: rittal.com/nz-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



DK 7824.225 - Sheet steel door for DK-TS

To replace existing doors. With 180° hinges and swivel handle with security lock no. 3524 E.

Features

Model No.	DK 7824.225
Product description	To replace existing doors. With 180° hinges and swivel handle with security lock no. 3524 E, in exchange for comfort handle.
Material	Sheet steel
Colour	RAL 7035
Supply includes	Assembly parts
IP protection category to IEC 60529	IP 55
To fit	Enclosure type: DK-TS Width: 600 mm Height: 2,200 mm
Packs of	1 pc(s).
Net weight	29.45 kg
Gross weight	31 kg
Customs tariff number	94039910
ETIM 9	EC000747
ECLASS 8.0	27182204

Tender text

TS steel sheet door

2 mm steel sheet door, with foamed-in seal, removable rectangular frame with 25 mm DIN pitch pattern punchings, locking rod with four locking points, swivel handle with 3524 E. Security lock A TS 8611.070 comfort handle can also be fitted as an option.

Hinge has captive hinge pins, the doorstop can be moved without having to remove the locking rods, 180° door opening angle.

Material: Sheet steel

Colour: RAL 7035

Dimensions: enclosures (W x H): W: 600 mm H: 2200 mm