

Rittal – The System.

Faster – better – everywhere.



DK 7824.382

Sheet steel door, vertically divided, vented

State: 15/03/2026 (Source: [rittal.com/nz-en](https://www.rittal.com/nz-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7824.382 - Sheet steel door, vertically divided, vented for DK-TS

To replace existing doors. Thanks to the minimal rotation radius of the individual doors, the distance between individual bayed enclosure suites may be reduced.

Features

Model No.	DK 7824.382
Product description	With 130° hinges and locking rod, including comfort handle for profile half-cylinders with security lock no. 3524 E. Thanks to the minimal rotation radius of the individual doors, the distance between individual bayed enclosure suites may be reduced. The extensive door perforations additionally support climate control of the installed equipment. Perforated surface with air inlet openings > 78%.
Material	Sheet steel
Supply includes	Assembly parts
IP protection category to IEC 60529	IP 20
To fit	Enclosure type: DK-TS Width: 800 mm Height: 2,200 mm
Packs of	1 pc(s).
ECLASS 8.0	27182204