

Rittal – The System.

Faster – better – everywhere.



TS 7825.382

Gland plate, multi-piece

State: 20/06/2025 (Source: [rittal.com/nz-en](https://www.rittal.com/nz-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 7825.382 - Gland plate, multi-piece for DK-TS

Gland plate, multi-piece for DK-TS, in accordance with the enclosure depth any combination is possible.

Features

| | |
|-----------------------|------------------------------------------------------------------------------------------------------------------------------------------|
| Model No. | TS 7825.382 |
| Product description | Any combination possible. |
| Material | Sheet steel |
| Surface finish | Zinc-plated |
| Supply includes | Pack of 1 set of gland plates including sliding plate for cable entry, sealing tape and assembly parts. |
| Note | For the size variant 800 x 800 mm, the gland plate included with the supply of pre-configured network racks should be additionally used. |
| To fit | Enclosure type: TS 8 Width: 800 mm Depth: 800 mm |
| Packs of | 1 set(s) |
| Net weight | 5 |
| Gross weight | 5.18 |
| Customs tariff number | 73269098 |
| EAN | 4028177302716 |
| ECLASS 8.0 | 27189261 |

Tender text

Multi-piece TS gland plate

For filling the base frame in a TS8 7 FR(i) enclosure, with base plates and a cable entry sliding plate with rubber cable clamp strip. Furthermore, the kit can be combined with the vented gland plate modules and the modules for cable entry purposes.

Dimension: For enclosures (WxD) 800 x 800 mm

Material: Sheet steel, zinc-plated