Rittal - The System.

Faster – better – everywhere.





TS 7826.605 Roof plate for cable entry, two-piece

State: 5/11/2025 (Source: rittal.com/nz-en)



TS 7826.605 - Roof plate for cable entry, two-piece for VX, VX IT, TS, TS IT

The two-piece design allows easy retro-fitting, by simply removing the front part of the plate for retrospective cable entry.



Features

Model No.	TS 7826.605
Product description	In exchange for the standard roof. Equipped with a sliding angular bracket in the rear section. Rubber cable clamp strip on both sides for attaching cable bundles and bunched cables. Due to the symmetrical design of the frame, side cable entry can also be achieved by rotating the roof plate. The two-piece design allows convenient retrofitting.
Material	Sheet steel
Colour	RAL 7035
To fit	Width: 600 mm Depth: 1,000 mm
Packs of	1 pc(s).
Net weight	8.443
Gross weight	8.887
Customs tariff number	94039910
EAN	4028177345355
E-Number Sweden	E7239740
ETIM 9	EC000744

© Rittal 2025

Features

ECLASS 8.0

27182405

Tender text

Cable entry roof plate for TS, TS IT $W \times D = 600 \times 1000$, two-piece

A cable entry roof plate including assembly parts.

Material: Sheet steel, spray finished in RAL 7035

Dimensions (W x D): 600 mm x 1000 mm

© Rittal 2025

3