

# Rittal – The System.

Faster – better – everywhere.



## TS 8184.235

## Side panel, screw-fastened, sheet steel

State: 23/08/2025 (Source: [rittal.com/nz-en](http://rittal.com/nz-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 8184.235 - Side panel, screw-fastened, sheet steel for TS, TS IT

Side panels, screw-fastened, sheet steel, for TS.

## Features

|                                     |  |
|-------------------------------------|--|
| Model No.                           | TS 8184.235  |
| Benefits                            | Automatic potential equalisation and higher EMC protection due to enclosure panel holders with earthing insert<br>Easy positioning with the location aid<br>Earthing bolt with contact surface |
| Material                            | Sheet steel, 1.5 mm  |
| Surface finish                      | Dipcoat-primed, powder-coated on the outside   |
| Colour                              | RAL 7035   |
| Supply includes                     | Assembly parts   |
| Note                                | Enclosure panel holders may optionally be fitted from the inside or outside of the enclosure<br>Area available for population: External dimension – 100 mm                                     |
| To fit                              | Enclosure type: TS<br>TS IT<br>Height: 1,800 mm<br>Depth: 400 mm   |
| IP protection category to IEC 60529 | IP 55  |
| Basic material                      | Sheet steel  |
| Packs of                            | 2 pc(s).   |
| Net weight                          | 16.6   |
| Gross weight                        | 17.8   |
| Customs tariff number               | 94039910   |
| EAN                                 | 4028177205215  |

# Features

|            |          |
|------------|----------|
| ETIM 9     | EC002524 |
| ECLASS 8.0 | 27182101 |

# Approvals

|              |                              |
|--------------|------------------------------|
| Explanations | Declaration of conformity UK |
|--------------|------------------------------|