

Rittal – The System.

Faster – better – everywhere.



TS 8602.080

Base/plinth trim panels, side, 200 mm

State: 23/05/2026 (Source: rittal.com/nz-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8602.080 - Base/plinth trim panels, side, 200 mm for base/plinth components front and rear

For mounting between the base/plinth components. At 200 mm height, two 100 mm base/plinth trims may be used.

Features

| | |
|-----------------------|--|
| Model No. | TS 8602.080 |
| Product description | For mounting between the base/plinth components. At 200 mm height, two 100 mm base/plinth trims may be used. |
| Material | Sheet steel |
| Surface finish | Spray-finished |
| Colour | RAL 7022 |
| Supply includes | 2 base/plinth trim panels Assembly parts |
| Assembly instruction | Base/plinth trim panels, side, 100 mm, may be installed rotated through 90° to stabilise bayed base/plinth components. The base/plinth baying bracket is required for this purpose |
| Dimensions | Height: 200 mm |
| To fit | Enclosure type: TS: = 800 mm Enclosure type: SE Enclosure type: CM Enclosure type: TP Enclosure type: PC Enclosure type: IW Enclosure type: TS IT |
| Packs of | 2 pc(s). |
| Net weight | 4.454 kg |
| Gross weight | 4.654 kg |
| Customs tariff number | 94039910 |
| ECLASS 8.0 | 27182003 |

Features

Product description

TS Trim panel, sides, H: 200 mm, for W: 800 mm, RAL 7022, sheet steel