

**Rittal – The System.**

Faster – better – everywhere.



**TS 8602.200**

**Base/plinth components, front and rear, 200 mm**

State: 23/05/2026 (Source: [rittal.com/nz-en](http://rittal.com/nz-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 8602.200 - Base/plinth components, front and rear, 200 mm Sheet steel, for TS, TS IT, SE, CM, TP, PC, IW, TE

Base/plinth component consisting of one trim panel and two pre-configured corner pieces. In 200 mm high base/plinth components, one trim panel is divided into two for cable entry.

## Features

|                       |   |
|-----------------------|---|
| Model No.             | TS 8602.200   |
| Design                | solid   |
| Product description   | Base/plinth component consisting of one trim panel and two pre-configured corner pieces. In 200 mm high base/plinth components, one trim panel is divided into two for cable entry. |
| Material              | Base/plinth components: Sheet steel<br>Cover caps: Plastic  |
| Surface finish        | Spray-finished  |
| Colour                | RAL 7022<br>Cover caps: RAL 9005  |
| Supply includes       | 2 base/plinth components<br>4 cover caps<br>Assembly parts  |
| Dimensions            | Height: 200 mm  |
| To fit                | Enclosure type: TS: = 1,200 mm<br>Enclosure type: SE<br>Enclosure type: CM<br>Enclosure type: TP<br>Enclosure type: PC<br>Enclosure type: IW<br>Enclosure type: TS IT               |
| Packs of              | 2 pc(s).  |
| Net weight            | 10.52 kg  |
| Gross weight          | 11.358 kg   |
| Customs tariff number | 94039910  |

# Features

---

ECLASS 8.0

27182003

---

Product description

TS Base/plinth component, front and rear, H: 200 mm, for W: 1200 mm, RAL 7022, sheet steel