## Rittal - The System.

Faster - better - everywhere.





# TS 8612.760 TS punched rail 25 x 38 mm

State: 12/11/2025 (Source: rittal.com/nz-en)



# TS 8612.760 - TS punched rail 25 x 38 mm

For heavy installations, with attachment holes. Installation options on the vertical TS enclosure section.





#### **Features**

Model No.	TS 8612.760
Product description	For heavy installations, with attachment holes.
Material	Sheet steel, 3.0 mm
Surface finish	Zinc-plated
Supply includes	Assembly screws
Installation options	On the vertical TS, VX SE enclosure section With 9 mm round holes all round on a 25 mm pitch pattern For the external mounting angle of support rails, system support rails, C rails 30/15, cable clamp rails (right angle section), own assemblies
Note	In conjunction with the snap-on nut, particularly well-suited for dynamic connections
To fit	To fit width/depth: 600 mm
Packs of	2 pc(s).
Net weight	1.648
Gross weight	1.96
Customs tariff number	73269098
EAN	4028177429147

© Rittal 2025

### Features

ECLASS 8.0

27189261

© Rittal 2025 3