### Rittal – The System.

Faster – better – everywhere.





# VX 8640.035 Base/plinth trim panels, side, 100 mm

State: 16/11/2025 (Source: rittal.com/nz-en)



# VX 8640.035 - Base/plinth trim panels, side, 100 mm for base/plinth system VX, sheet steel

To finish off a base/plinth unit at the sides and for additional stability, or for the interior installation of bayed base/plinths. One 200 mm high or two 100 mm high trim panels may optionally be fitted on 200 mm high base/plinths.

#### **Features**

Model No.	VX 8640.035
Product description	To finish off a base/plinth unit at the sides and for additional stability, or for the interior installation of bayed base/plinths. One 200 mm high or two 100 mm high trim panels may optionally be fitted on 200 mm high base/plinths.
Material	Sheet steel
Colour	RAL 9005
Supply includes	Assembly parts
Dimensions	Height: 100 mm
To fit	Enclosure type: VX TX CableNet Depth: = 1,000 mm
Type rating to UL 50E	Type 1, 12
Weight/pack	3.3 kg
Packs of	2 pc(s).
Net weight	2.442
Gross weight	3.382
Customs tariff number	94039910
EAN	4028177958975
E-Number Sweden	E3465381
ETIM 9	EC000721
ECLASS 8.0	27182003

© Rittal 2025 2

## Approvals

Approvals

UL + C-UL - FTTA

© Rittal 2025 3