

# Rittal – The System.

Faster – better – everywhere.



## TS 8700.850

# Side panels, screw-fastened, stainless steel

State: 23/05/2026 (Source: [rittal.com/nz-en](http://rittal.com/nz-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 8700.850 - Side panels, screw-fastened, stainless steel for TS

Side panels, screw-fastened, stainless steel, for TS.



## Features

Model No.	TS 8700.850
Benefits	Automatic potential equalisation and higher EMC protection due to enclosure panel holders with earthing insert Easy positioning with the location aid Earthing bolt with contact surface
Material	Stainless steel 1.4301 (AISI 304), 1.5 mm
Surface finish	Brushed, grain 400
Supply includes	Assembly parts
To fit	Enclosure type: TS Height: = 1,800 mm Depth: = 500 mm
IP protection category to IEC 60529	IP 55
Basic material	Stainless steel

# Features

Packs of	2 pc(s).
Net weight	11.116 kg
Gross weight	23.7 kg
Customs tariff number	94039910
ECLASS 8.0	27182101
Product description	TS Side panel, screw-fastened, for TS, for WD: 40x40 mm, Stainless steel 1.4301

## Tender text

Side panel, screw-fastened, stainless steel TS  
Screw-fastened side panel, easy positioning on the frame with the location aid.

Automatic potential equalisation and higher EMC protection thanks to enclosure panel fasteners with contact elements.

Protection category IP 55 to IEC 60529.

Hinged version (option), max. opening angle 180°.

Material: Stainless steel 1.4301 (AISI 304), 1.5 mm

Surface finish: Brushed, grain 400

for enclosure dimensions: H: 1800 mm D: 500 mm

Side panel, screw-fastened, stainless steel 8700.850