Rittal - The System.

Faster – better – everywhere.





TS 8700.850

Side panels, screw-fastened, stainless steel

State: 12/11/2025 (Source: rittal.com/nz-en)



TS 8700.850 - Side panels, screw-fastened, stainless steel for TS

Side panels, screw-fastened, stainless steel, for TS.



Features

Model No.	TS 8700.850
Benefits	Automatic potential equalisation and higher EMC protection due to
	enclosure panel holders with earthing insert
	Easy positioning with the location aid
	Earthing bolt with contact surface
Material	Stainless steel 1.4301 (AISI 304), 1.5 mm
Surface finish	Brushed, grain 400
Supply includes	Assembly parts
To fit	Enclosure type: TS
	Height: = 1,800 mm
	Depth: = 500 mm
IP protection category to IEC 60	IP 55
529	
Basic material	Stainless steel
Basic material	Stainless steel

© Rittal 2025

Features

Packs of	2 pc(s).
Net weight	11.116
Gross weight	23.7
Customs tariff number	94039910
EAN	4028177300095
ECLASS 8.0	27182101

Tender text

Side panel, screw-fastened, stainless steel TS Screw-fastened side panel, easy positioning on the frame with the location aid.

Automatic potential equalisation and higher EMC protection thanks to enclosure panel fasteners with contact elements.

Protection category IP 55 to IEC 60529.

Hinged version (option), max. opening angle 180°.

Material: Stainless steel 1.4301 (AISI 304), 1.5 mm

Surface finish: Brushed, grain 400

for enclosure dimensions: H: 1800 mm D: 500 mm Side panel, screw-fastened, stainless steel 8700.850

© Rittal 2025 3