

# Rittal – The System.

Faster – better – everywhere.



## DK 9055.312 Monitor/keyboard unit

State: 6/04/2026 (Source: rittal.com/nz-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 9055.312 - Monitor/keyboard unit with 17" TFT display and VGA/DVI connection

1 U chassis with 17" TFT display, English or German keyboard layout, with telescopic slides.



## Features

Model No.	DK 9055.312
Product description	The unit is housed in a pull-out drawer. The monitor can be flipped up and the drawer latches into the end position. This means that the unit only requires 1 U in the 482.6 mm (19") rack.
Benefits	Analog and digital video input Cables are safely routed in the energy chain Lockable at the front Simple, one-man installation.
Colour	RAL 7035
Supply includes	Monitor/keyboard unit, 1 U VGA cable DVI cable USB cable Earthing-pin mains cable with 17" TFT display and VGA/DVI connection 2 PS/2 cables Keyboard with integral touchpad
Rated operating voltage	100 V - 240 V, 1~, 50 Hz/60 Hz
Max. power consumption with closed monitor unit	1 W

# Features

Max. power consumption in operation	32 W
Interfaces	VGA (D-Sub HD 15-pole) DVI 1 x USB PS/2
Connector (type)	IEC 320 connector C14
Layout	US English
Dimensions	Width: 482.6 mm Depth: 680 mm
Operating temperature range	5 °C...45 °C
Installation dimensions	Installation depth (min.): 680 mm Installation depth (max.): 850 mm
Display features	Diagonal: 432 mm (17") Format: 4 : 3 Contrast ratio: Contrast ratio approx. 1000:1 Display brightness: 350 cd/m <sup>2</sup> Resolution of display: 1280 x 1024 pixels Number of colours: 16,700,000
Packs of	1 pc(s).
Net weight	15.85 kg
Gross weight	17.25 kg
Customs tariff number	85286200
ETIM 9	EC001428
ECLASS 8.0	19200201
Product description	DK Monitor/keyboard unit, WHD: 482.6 mm (19")x1 Ux680 mm, 100-240 V, 1~, 50/60 Hz, US-english, RAL 7035

# Approvals

Explanations	Declaration of conformity
--------------	---------------------------