Rittal – The System.

Faster - better - everywhere.





DK 9055.410 Monitor/keyboard unit

State: 9/12/2025 (Source: rittal.com/nz-en)



DK 9055.410 - Monitor/keyboard unit with 17" TFT display and VGA/DVI connection

1 U chassis with 17" TFT display, English or German keyboard layout, with telescopic slides.



Features

Model No.	DK 9055.410
Product description	The unit is housed in a pull-out drawer. The monitor can be flipped up and the drawer latches into the end position. This means that the unit only requires 1 U in the 482.6 mm (19") rack.
Benefits	Analog and digital video input
	Cables are safely routed in the energy chain
	Lockable at the front
	Simple, one-man installation.
Colour	RAL 9005
Supply includes	Monitor/keyboard unit, 1 U
	VGA cable
	DVI cable
	USB cable
	Earthing-pin mains cable
	with 17" TFT display and VGA/DVI connection
	2 PS/2 cables
	Keyboard
	with integral touchpad
Rated operating voltage	100 V - 240 V, 1~, 50 Hz/60 Hz
Max. power consumption with closed monitor unit	1 W

© Rittal 2025

Features

Max. power consumption in operation	32 W
Interfaces	VGA (D-Sub HD 15-pole) DVI 1 x USB
Connector (type)	PS/2 IEC 320 connector C14
	TEC 320 Conflector C14
Layout	German
Note on Model No.	Extended delivery times.
Dimensions	Width: 482.6 mm Depth: 680 mm
Operating temperature range	5 °C45 °C
Installation dimensions	Installation depth (min.): 680 mm Installation depth (max.): 850 mm
Display features	Diagonal: 432 mm (17") Format: 4:3 Contrast ratio: Contrast ratio approx. 1000:1 Display brightness: 350 cd/m² Resolution of display: 1280 x 1024 pixels Number of colours: 16,700,000
Packs of	1 pc(s).
Net weight	15.827
Gross weight	16.66
Customs tariff number	85286200
EAN	4028177638396
ETIM 9	EC001428
ECLASS 8.0	19200201

Approvals

© Rittal 2025 3

Approvals

Explanations

Declaration of conformity

© Rittal 2025