

Rittal – The System.

Faster – better – everywhere.



DK 9055.412

Monitor/keyboard unit

State: 14/08/2025 (Source: rittal.com/nz-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 9055.412 - Monitor/keyboard unit with 17" TFT display and VGA/DVI connection

1 U chassis with 17" TFT display, English or German keyboard layout, with telescopic slides.



Features

| | |
|---|---|
| Model No. | DK 9055.412 |
| Benefits | Analog and digital video input Cables are safely routed in the energy chain Lockable at the front Simple, one-man installation. |
| Colour | RAL 9005 |
| Supply includes | Monitor/keyboard unit, 1 U VGA cable DVI cable USB cable Earthing-pin mains cable with 17" TFT display and VGA/DVI connection 2 PS/2 cables Keyboard with integral touchpad |
| Rated operating voltage | 100 V - 240 V, 1~, 50 Hz/60 Hz |
| Max. power consumption with closed monitor unit | 1 W |
| Max. power consumption in operation | 32 W |

Features

| | |
|-----------------------------|---|
| Interfaces | VGA (D-Sub HD 15-pole) DVI 1 x USB PS/2 |
| Connector (type) | IEC 320 connector C14 |
| Layout | US English |
| Note on Model No. | Extended delivery times. |
| Dimensions | Width: 482.6 mm Depth: 680 mm |
| Operating temperature range | 5 °C...45 °C |
| Installation dimensions | Installation depth (min.): 680 mm Installation depth (max.): 850 mm |
| Display features | Diagonal: 432 mm (17") Format: 4 : 3 Contrast ratio: Contrast ratio approx. 1000:1 Display brightness: 350 cd/m² Resolution of display: 1280 x 1024 pixels Number of colours: 16,700,000 |
| Packs of | 1 pc(s). |
| Net weight | 15.5 |
| Gross weight | 16.5 |
| Customs tariff number | 85286200 |
| EAN | 4028177638402 |
| ETIM 9 | EC001428 |
| ECLASS 8.0 | 19200201 |

Approvals

| | |
|--------------|---------------------------|
| Explanations | Declaration of conformity |
|--------------|---------------------------|