


Rittal – The System.

Faster – better – everywhere.



SV 9342.030

Busbar support

State: 8/01/2026 (Source: rittal.com/nz-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SV 9342.030 - Busbar support 1-pole



Features

Model No.	SV 9342.030
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Supply includes	Including raised section for stepped configuration of the PLS busbars
To fit busbars	PLS 1600
Number of poles	Single-pole
Note	Multi-pole systems with 60 mm bar centre distance may be configured by baying the busbar supports Support suitable for AC and DC applications.
Rated operating voltage	1000 V, 1~ 1500 V (DC)
PEN/N/PE support	Yes
Packs of	4 pc(s).
Net weight	0.28
Gross weight	0.306
Customs tariff number	85469010
EAN	4028177614925
ETIM 9	EC001166

Features

ECLASS 8.0 27400607

Approvals

Approvals	ABS Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Declaration of conformity

Tender text

PLS 1600 busbar support 1-pole

PLS 1600 busbar support with fastening attachment,
1-pole

Technical specifications

Bar centre distance: 60 mm

E-Cu busbar :PLS 1600

Construction width: 40 mm

Length: 60 mm

Tightening torque

Assembly screw: 3 - 5 Nm

Lid attachment: 0.7 Nm

System

Rittal RiLine60