


Rittal – The System.

Faster – better – everywhere.



SV 9346.060

NH slimline fuse-switch disconnecter

State: 16/05/2024 (Source: rittal.com/nz-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9346.060 - NH slimline fuse-switch disconnecter



Features

Model No.	SV 9346.060
Material	Fibreglass-reinforced polyamide Fire protection corresponding to UL 94-V0 Contact tracks: Silver-plated hard copper
Colour	Chassis: RAL 7035 Cover: RAL 7001 Handle: RAL 7016
For bar systems with centre-to-centre spacing	100 mm
Cable outlet	Top/bottom
Type of electrical connection	Screw M8
Rated operating current max.	160 A
For NH size	00
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (fuse inserts)
For converter installation	Yes
Dimensions	Width: 50 mm Height: 400 mm
Connection for round conductor cross-sections	2.5 - 95 mm ²
To fit busbars	Height: 5, 10 mm

Features

Rated operating voltage	690 V, 3~
Number of poles	3-pole
Packs of	1 pc(s).
Weight/pack	1.18 kg
Copper weight (kg per piece)	0.65
Customs tariff number	85365080
EAN	4028177668133
ETIM 7.0	EC001046
ECLASS 8.0	27371402

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---