

Rittal – The System.

Faster – better – everywhere.



SV 9613.000

**Mini-PLS busbar connection
adaptor**

State: 24/06/2026 (Source: rittal.com/nz-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9613.000 - Mini-PLS busbar connection adaptor

Rated current 63 A/1600 A/250 A, cable outlet top/bottom

Features

| | |
|---|---|
| Model No. | SV 9613.000 |
| Material | Polyamide Fire protection corresponding to UL 94-V0 |
| Colour | RAL 7035 Chassis: RAL 9011 |
| Clamping area for laminated copper bars (W x H) | 10 x 8 mm |
| Note | Wire end ferrules should be used with fine wire conductors |
| Cable outlet | Top/bottom |
| Rated operating voltage | 690 V |
| Rated current max. | 63 A |
| Dimensions | Width: 54 mm Height: 160 mm |
| Connection of round conductors | 1.5 - 35 mm ² |
| Packs of | 1 pc(s). |
| Net weight | 0.37 kg |
| Gross weight | 0.397 kg |
| Copper weight (kg per piece) | 0.081 |
| Customs tariff number | 85369010 |
| ETIM 9 | EC001531 |
| ECLASS 8.0 | 27370304 |
| Product description | SV Mini-PLS busbar connection adaptor, 63 A, 690 V, 3-pole, round conductor connection 1,5-35 mm ² , clamping area WH: 10x8 mm |

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK