

**Rittal – The System.**

Faster – better – everywhere.



**SV 9613.000**

**Mini-PLS busbar connection  
adaptor**

State: 8/05/2026 (Source: [rittal.com/nz-en](http://rittal.com/nz-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9613.000 - Mini-PLS busbar connection adaptor

Rated current 63 A/1600 A/250 A, cable outlet top/bottom

## Features

Model No.	SV 9613.000
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7035 Chassis: RAL 9011
Clamping area for laminated copper bars (W x H)	10 x 8 mm
Note	Wire end ferrules should be used with fine wire conductors
Cable outlet	Top/bottom
Rated operating voltage	690 V
Rated current max.	63 A
Dimensions	Width: 54 mm Height: 160 mm
Connection of round conductors	1.5 - 35 mm <sup>2</sup>
Packs of	1 pc(s).
Net weight	0.37 kg
Gross weight	0.397 kg
Copper weight (kg per piece)	0.081
Customs tariff number	85369010
ETIM 9	EC001531
ECLASS 8.0	27370304
Product description	SV Mini-PLS busbar connection adaptor, 63 A, 690 V, 3-pole, round conductor connection 1,5-35 mm <sup>2</sup> , clamping area WH: 10x8 mm

# Approvals

---

Explanations

Declaration of conformity

Declaration of conformity UK