

# Rittal – The System.

Faster – better – everywhere.



## SV 9617.000

## Mini-PLS component adaptor

State: 5/07/2026 (Source: [rittal.com/nz-en](http://rittal.com/nz-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9617.000 - Mini-PLS component adaptor

Maximum rated current from 12 A to 100 A.

## Features

Model No.	SV 9617.000
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Connection cables (AWG)	AWG 10
Rated operating voltage	690 V, 3~
Rated current max.	40 A
Dimensions	Width: 54 mm Height: 160 mm
Support rails Qty/height	1 / 15 mm
To fit manufacturer (model)	ABB Eaton MS450 max. 40 A PKZM4 max. 40 A
Packs of	1 pc(s).
Net weight	0.33 kg
Gross weight	0.374 kg
Copper weight (kg per piece)	0.046
Customs tariff number	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304
Product description	SV Mini-PLS component adaptor, 40 A, 690 V, 3-pole, connection cable AWG 10, WH: 54x160 mm, support rail H: 15 mm

# Approvals

---

Approvals	UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK

---