

Rittal – The System.

Faster – better – everywhere.



SV 9635.330 Component adaptor

State: 27/07/2025 (Source: rittal.com/nz-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9635.330 - Component adaptor 3-pole

For assembly of switchgear and protective gear.

Features

| | |
|------------------------------|--|
| Model No. | SV 9635.330 |
| Design | Comfort |
| Function principle | For mechanical attachment and direct contacting of electrical equipment on the board |
| Material | Polyamide Fire protection corresponding to UL 94 |
| Colour | RAL 7035 |
| Note | The technical data may vary for UL applications |
| Rated current max. | 16 A |
| Rated operating voltage | 600 V (DC), 3~ 690 V (AC), 3~ |
| Number of poles | 3-pole |
| Electrical ratings UL | Rated operating voltage (max.) UL: 600 V AC |
| Connection cables (AWG) | AWG 14 |
| Length of connection cable | 160 mm |
| Support rails Qty/height | 1 / 10 mm |
| Support rail type | adjustable |
| Dimensions | Width: 45 mm Height: 160 mm Depth: 34.5 mm |
| Packs of | 4 pc(s). |
| Net weight | 0.44 |
| Gross weight | 0.494 |
| Copper weight (kg per piece) | 0.026 |

Features

| | |
|-----------------------|---------------|
| Customs tariff number | 85369095 |
| EAN | 4028177817357 |
| ETIM 9 | EC001531 |
| ECLASS 8.0 | 27370304 |

Approvals

| | |
|--------------|---|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity Declaration of conformity UK |