

# Rittal – The System.

Faster – better – everywhere.



## SV 9666.550

# NH slimline fuse-switch-disconnector module

State: 22/05/2026 (Source: [rittal.com/nz-en](http://rittal.com/nz-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9666.550 - NH slimline fuse-switch-disconnector module

For NH slimline fuse-switch disconnectors, sizes 00 to 3 (3-pole, 100/185 mm bar centre distance).

## Features

|                                     |  |
|-------------------------------------|--|
| Model No.                           | SV 9666.550  |
| Product description                 | For NH slimline fuse-switch disconnectors, sizes 00 to 3 (3-pole, 100/185 mm bar centre distance).   |
| Material                            | Cover: Polystyrene<br>Holder: Fibreglass-reinforced plastic  |
| Colour                              | RAL 7035   |
| Supply includes                     | Assembly parts   |
| Note                                | In order to ensure problem-free cable connection, a contact hazard protection module or an N/PE busbar module must be installed above or below the NH slimline fuse-switch disconnector modules. |
| Dimensions                          | Width: 500 mm<br>Height: 750 mm  |
| Size                                | Width units (WU) @ 250 mm: 2<br>Height units (U) @ 150 mm: 5   |
| For size                            | 8 x Gr. 00<br>4 x Gr. 1<br>4 x Gr. 2<br>4 x Gr. 3  |
| To fit Model No.                    | 9677.XXX   |
| To fit busbars                      | 40 x 10<br>50 x 10<br>60 x 10  |
| Centre-to-centre spacing of busbars | 185 mm   |
| Packs of                            | 1 pc(s).   |

# Features

---

|                       |   |
|-----------------------|---|
| Net weight            | 3.84 kg   |
| Gross weight          | 3.89 kg   |
| Customs tariff number | 85369095  |
| ETIM 9                | EC001893  |
| ECLASS 8.0            | 27400608  |
| Product description   | SV NH fuse-switch disconnecter module (ISV), 2 WU (500 mm), 5 U (750 mm), for 8 x size 00, 4 x size 1-3, (SV 9346XXX, 185 mm) |

# Approvals

---

|              |   |
|--------------|---|
| Explanations | Declaration of conformity<br>Declaration of conformity UK |
|--------------|---|