

# Rittal – The System.

Faster – better – everywhere.



## BG 1559.510 Bus enclosures BG

State: 23/05/2026 (Source: [rittal.com/ro-ro](http://rittal.com/ro-ro))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# BG 1559.510 - Bus enclosures BG

Wall-mounted enclosure with door of sheet steel, with polycarbonate viewing window. Protection category IP 65. Bus modules of virtually all makes may be attached.

## Features

Model No.	BG 1559.510
Material	Enclosure: Sheet steel Door: Sheet steel Viewing window: Polycarbonate, 4 mm
Surface finish	Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint
Colour	RAL 7035
Supply includes	Enclosure with door Viewing window in the door Gland plate in enclosure base
Protection category NEMA	NEMA 12
Protection category to IEC 60 529	IP 65
IK Code	IK08
Dimensions	Width: 600 mm Height: 200 mm Depth: 125 mm
Material thickness - enclosure	1,25 mm
Material thickness - door	1,25 mm
Door hinge position	bottom
Number of support rails	1
Lock	Lock version: Quick-release fastener including plastic bushes Number of locks: 3
Basic material	Sheet steel
Packs of	1 pc(s).

# Features

---

Net weight	5,066 kg
Gross weight	5,333 kg
Customs tariff number	94032080
ECLASS 8.0	27180101
Product description	BG Bus enclosure, WHD: 600x200x125 mm, Sheet steel, with gland plate in the base and support rails, Door with viewing window, hinged at bottom

# Approvals

---

Approvals	Lloyds Register UL + C-UL (listed)
Explanations	Declaration of conformity