

Rittal – The System.

Faster – better – everywhere.



KL 1582.000

Plastic cable gland plates

State: 02/08/2025 (Source: [rittal.com/ro-ro](https://www.rittal.com/ro-ro))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



KL 1582.000 - Plastic cable gland plates with PG knockouts

With pre-punched PG holes for cable glands.



Features

Model No.	KL 1582.000
Product description	With pre-punched PG holes for cable glands. Use seal for standard gland plates.
Material	ABS
Colour	RAL 7035
Note	The allocation of gland plate sizes is indicated on the relevant enclosures
No. of metric knockouts	6 2 2
Number x PG diameter	6 x 13.5 2 x 16 2 x 21
Dimensions	Width: 220 mm Depth: 90 mm
To fit	Enclosure type: KL
Gland plate	Size: 2
Operating temperature range	-40 °C...70 °C

Features

Protection category to IEC 60 529	IP 55 if installed correctly
Number knockouts	6 2 2
Packs of	5 pc(s).
Net weight	0.5
Gross weight	0.581
Customs tariff number	73269098
EAN	4028177010901
E-Number Sweden	E3404716
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421