


# Rittal – The System.

Faster – better – everywhere.



## AX 2260.640

## AX wall-mounted enclosure, 3-part

State: 01/08/2025 (Source: [rittal.com/ro-ro](https://www.rittal.com/ro-ro))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AX 2260.640 - AX wall-mounted enclosure, 3-part

The delivery concept of the three-part AX wall-mounted enclosures reduces complexity and enhances flexibility. The AX/VX modular system makes these enclosures suitable for a range of applications. The three-part structure ensures easy access.



## Features

|                 |  |
|-----------------|--|
| Model No.       | AX 2260.640  |
| Design          | Wall-mounted enclosures IT   |
| Material        | Wall and hinged part: Sheet steel, 1.5 mm<br>Viewing window: Single-pane safety glass, 3 mm  |
| Surface finish  | Powder-coated  |
| Colour          | Wall and hinged part: RAL 7035<br>Glazed door: RAL 7035/7015 (slate grey)  |
| Supply includes | Wall section: Gland plate, solid, top and bottom<br>Hinged part with 25 mm pitch pattern of holes in the front and rear frame, and two 482.6 mm (19") mounting angles, front, static installation<br>Designer glazed door<br>Centre part lock: 3 mm double-bit<br>Designer glazed door lock: Security lock 3524 E<br>Mini-comfort handle |
| Units           | 6 U  |

# Features

|  |  |
|--|--|
| Dimensions                             | Width: 600 mm<br>Height: 345 mm<br>Depth: 473 mm   |
| Number of locks                        | 1  |
| Load capacity of hinged part (static)  | 300 N  |
| Load capacity of wall section (static) | 100 N  |
| Basic material                         | Sheet steel  |
| Lock                                   | Lock version: Mini-comfort handle<br>Lock insert: Security lock insert no. 3524 E                              |
| Protection category to IEC 60 529      | IP 54 in conjunction with solid gland plate top and bottom   |
| Packs of                               | 1 pc(s).   |
| Net weight                             | 25.4   |
| Gross weight                           | 26.4   |
| Note on PCF category                   | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number                  | 94032080   |
| EAN                                    | 4028177983151  |
| ETIM 9                                 | EC002500   |
| ETIM 8                                 | EC002500   |
| ECLASS 8.0                             | 27180101   |

## Tender text

AX wall-mounted enclosure 3-part, 6 U, depth 473 mm

Enclosure: 3-part wall-mounted enclosure consisting of:  
Wall section with solid gland plate at the top and bottom, may optionally be exchanged for cable entry variants (accessories), holes for wall-mounting,

Hinged section with 2 pcs. 482,6 mm (19")  
mounting angles fitted at the front with all-around  
25 mm pitch pattern in the front and rear frame.  
Designer glazed door with mini-comfort handle  
for lock inserts, with security lock 3524 E,  
may optionally be exchanged for mini-comfort handle for  
semi cylinder (accessory)  
Material enclosure: sheet steel 1,5 mm,  
Material glazed door: single-pane safety glass, 3 mm  
Surface finish: powder-coated  
Color wall and hinged part: RAL 7035  
Color glazed door: RAL 7035/7015 (slate grey)  
Protection category: IP 55 nach EN 60 529  
Dimension (W x H x D): 600 x 345 x 473 mm, 6 U  
Manufacturer: Rittal GmbH & Co. KG