## Rittal – The System.

Faster – better – everywhere.





# AX 2262.160 AX wall-mounted enclosure, 3-part

State: 17/09/2025 (Source: rittal.com/ro-ro)



## AX 2262.160 - AX wall-mounted enclosure, 3-part

The delivery concept of the three-part AX wall-mounted enclosures reduces complexity and enhances flexibility. The AX/VX modular system makes these enclosures suitable for a range of applications. The three-part structure ensures easy access.



#### Features

Model No.	AX 2262.160
Design	Wall-mounted enclosures IT
Material	Wall and hinged part: Sheet steel, 1.5 mm
	Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
Colour	Wall and hinged part: RAL 7035
	Glazed door: RAL 7035/7015 (slate grey)
Supply includes	Wall section: Gland plate, solid, top and bottom
	Hinged part with 25 mm pitch pattern of holes in the front and rear
	frame, and two 482.6 mm (19") mounting angles, front, static
	installation
	Designer glazed door
	Centre part lock: 3 mm double-bit
	Designer glazed door lock: Security lock 3524 E
	Comfort handle for lock inserts and 2-point locking
Units	21 U

### Features

Dimensions	Width: 600 mm
	Height: 1,012 mm
	Depth: 673 mm
Number of locks	1
Load capacity of hinged part (static)	750 N
Load capacity of wall section (static)	250 N
Basic material	Sheet steel
Lock	Lock version: Comfort handle and 2-point locking
	Lock insert: Security lock insert no. 3524 E
Protection category to IEC 60 529	IP 54 in conjunction with solid gland plate top and bottom
Packs of	1 pc(s).
Net weight	55
Gross weight	56.5
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94032080
EAN	4028177983304
ETIM 9	EC002500
ETIM 8	EC002500
ECLASS 8.0	27180101

## Approvals

Explanations

Declaration of conformity

## Tender text

AX wall-mounted enclosure 3-part, 21 U, depth 673 mm

Enclosure: 3-part wall-mounted enclosure consisting of: Wall section with solid gland plate at the top and bottom, may optionally be exchanged for cable entry variants (accessories), holes for wall-mounting, Hinged section with 2 pcs. 482,6 mm (19") mounting angles fitted at the front with all-around 25 mm pitch pattern in the front and rear frame. Designer glazed door with comfort handle for lock inserts, with security lock 3524 E, may optionally be exchanged for comfort handle for semi cylinder (accessory) Material enclosure: sheet steel 1,5 mm, Material glazed door: single-pane safety glass, 3 mm Surface finish: powder-coated Color wall and hinged part: RAL 7035 Color glazed door: RAL 7035/7015 (slate grey) Protection category: IP 55 nach EN 60 529 Dimension (W x H x D): 600 x 1012 x 673 mm, 21 U Manufacturer: Rittal GmbH & Co. KG